

Integrated Optics, UAB Company code: 302833442 VAT No: LT100007179012 https://integratedoptics.com info@integratedoptics.com



PART NUMBER 0785L-26A ITEM NAME 785 NM SLM LASER (DIODE SMA PORT)

# PRODUCT DATASHEET



### DESCRIPTION

785 nm laser with SMA output is a very compact high performance laser source for multimode fiber installations. Fiber could be supplied optionally.

### Note:


In optical systems with strong back-reflections (e.g. more than 10%), the laser must be protected by using an optical isolator with at least 20 dB isolation. Typical applications include interferometry, confocal microscopy (especially working with reflective samples), etc. Failure to comply with these requirements will render the warranty void for cases of COD (Catastrophic Optical Damage) of laser diode facets.

# **SPECIFICATIONS**

Specifications updated: 6 September 2021


Parameter	Minimum Value	Typical Value	Maximum Value
Central Wavelength, nm	784.7	784.8	785.1
Longitudinal modes	-	Single	-
Spectral line width FWHM, pm	-	0.1	1
Output power, mW	-	100 <sup>1</sup>	120
Side-mode suppression ratio (SMSR), dB	40	50	60
Fiber coupling efficiency, %	50	70 <sup>2</sup>	80
Fiber core diameter, μm	50	105	200
Power stability, % (RMS, 8 hrs)	0.02	0.05 <sup>3</sup>	0.25
Power stability, % (peak-to-peak, 8 hrs)	0.1	0.3 4	1
Intensity noise, % (RMS, 20 Hz to 20 MHz)	0.1	0.25 <sup>5</sup>	0.6
Control interface type	-	UART <sup>6</sup>	-
Transversal modes	-	Multiple	-
Operation mode	-	APC (CW)	-
Modulation bandwidth, MHz	-	N/A <sup>7</sup>	-
Input voltage, VDC	4.8	5	5.3
External power supply requirement	-	+5 V DC, 1.5 A	-
Dimensions, mm	-	50 x 30 x 18 <sup>8</sup>	-
Heat-sinking requirement, °C/W	-	1	-
Optimum heatsink temperature, °C	15	20	30
Warm up time, mins (cold start)	0.1	0.5	1
Temperature stabilization	-	Internal TEC	-
Overheat protection	-	Yes	-

## TYPICAL SPECTRUM



Typical spectrum of 0785 nm diode laser. Measured with 20 pm resolution.

### **DRAWING**



condensing)  Net weight, kg	).4	0.12 2 14 (10000) <sup>9</sup> Yes	<ul><li>50</li><li>0.14</li><li>10</li><li>-</li></ul>
Max. power consumption, W 0 Warranty, months (op. hrs) - RoHS -	).4	2 14 (10000) <sup>9</sup>	10
Warranty, months (op. hrs) - RoHS -		14 (10000) <sup>9</sup>	
RoHS -			-
		Voc	
CE compliance -		165	-
		- General Product Safety Directive (GPSD) 2001/95/EC - (EMC) Directive 2004/108/EC	-
Laser Safety Class -		3B	-
OEM lasers are not compliant with -		IEC60825- 1:2014 (compliant using additional accessories)	-
Country of origin -		Lithuania	-

<sup>&</sup>lt;sup>1</sup> The optical power can be tuned from virtually 0% to 100%. However, other specifications, such as central wavelength, power stability, noise, polarization ratio, beam shape, quality and circularity are not guaranteed at power levels other than factory preset power. Significantly worse power stability is to be expected at very low power levels, e.g. <3% from specified nominal power.

Note: Product specifications are subject to change without prior notice to improve reliability, function or design or otherwise.

 $<sup>^2\</sup>mbox{Output}$  power is heavily dependent on fiber insertion repeatability.

<sup>&</sup>lt;sup>3</sup>The long term power test is carried out at constant laser body temperature (+/-0.1 °C) using an optical power meter with an input bandwidth of 10 Hz. The actual measurement rate has a period of about 20 seconds to 1 minute.

<sup>&</sup>lt;sup>4</sup>The long term power test is carried out at constant laser body temperature (+/-0.1 °C) using an optical power meter with an input bandwidth of 10 Hz. The actual measurement rate has a period of about 20 seconds to 1 minute.

 $<sup>^5</sup>$  Noise level is measured with a fast photodiode connected to an oscilloscope. The overall system bandwidth is from 2 kHz to 20 MHz.

 $<sup>^{6}</sup>$  Break-out-boxes AM-C8 and AM-C3 can be used for conversion of UART communication to either USB or RS232.

 $<sup>^7\,\</sup>rm TTL$  digital modulation up to 10 MHz.

<sup>&</sup>lt;sup>8</sup> Excluding control interface pins and an output window/fiber assembly.

<sup>&</sup>lt;sup>9</sup> Whichever occurs first. The laser has an integrated operational hours counter.